



## **PAMAS S40 GO AVTUR**

# **Rugged and Portable Particle Counter for Aviation Turbine Fuel & Diesel**

The PAMAS S40 GO AVTUR is a special version of the portable particle counter PAMAS S40 AVTUR.

The PAMAS S40 AVTUR has its own IP method (IP577), that was drafted, validated and published by the Energy Institute in London.

This guarantees highest quality of the method and best compatibility with other methods for contamination control. The method IP 577 has been included in revision 7 of the DEF STAN 91-091 published by the UK Ministry of Defence.

#### **Applications:**

- Online measurements at pressureless systems or at live systems up to 6 bar
- Offline measurement using sample bottles (laboratory mode)
- Long term analysis
- Bypass filtration monitoring
- Filter verification

#### **Key features:**

- 8 channel high resolution digital system for analysis (up to 32 channels available upon request)
- Fully compliant with the standard methods IP 577 and IP PM FA of the Energy Institute London
- Fully compliant with the standard DEF STAN 91-091 of the UK Ministry of Defence
- Reporting of six ISO 4406-codes 4  $\mu\text{m(c)}$ , 6  $\mu\text{m(c)}$ , 14  $\mu\text{m(c)}$ , 21  $\mu\text{m(c)}$ , 25  $\mu\text{m(c)}$  and 30  $\mu\text{m(c)}$  in accordance with DEFSTAN 91-091
- from pressureless to pressurised sampling up to 6 bar
- User-friendly operation using touch screen with graphic display



# PAMAS S40 GO AVTUR

## Rugged particle counter for on-site measurements in harsh environment



- The volumetric cell design of PAMAS sensors guarantees highest accuracy, resolution and best statistical information
- Measuring results reported in compliance with IP 577, DEF STAN 91-91, ISO 4406, NAS 1638, SAE AS 4059, GJB 420, GOST 17216 and NAVAIR 01-1A-17
- Real portability with lab system accuracy
- Users can configure the system profile according to their needs
- Pressurised sensor avoids formation of bubbles
- Display and printout provide triple ISO codes, NAS- and SAE cleanliness classes, measurement volumes and particle numbers
- Highest repeatability and accuracy
- Password protected user levels
- Data storage of more than 4000 measurements
- Real time sample measurement data can be printed during the analysis and also be revisited and printed at anytime at a later date.
- User-friendly download software
- Operates on alternating current (90 - 240 V / 50 - 60 Hz AC) or on direct current (12 - 30 V DC) or with internal battery (for up to three hours operation)
- equipped with a sampling probe for batch sampling

The **PAMAS S40 GO AVTUR** is a portable system designed to count and size particles in fuels and aviation turbine fuel. A backlit touch screen for menu guided user access, and an additional membrane keypad give easy operation. An integrated printer provides instant hard copies of measurement results. Data files are compatible with most spreadsheet software.

Highly versatile due to a powerful 32-bit microprocessor allowing multiple automated sampling and data storage. User-friendly download software for transfer of stored measurement data to a PC as a basic feature.

Standard languages are English, German, French, Finnish, Dutch, Spanish, Hungarian, Russian, Chinese and Portuguese.



*For batch sampling, the PAMAS S40 GO AVTUR is equipped with a sampling probe.*

### Single particle counting system using volumetric sensor cells

A highly sophisticated sensor cell and optics guarantees best resolution and accuracy even under high pressure conditions.

Particle counting can be achieved using many methods, but only the use of volumetric cells, like those used in PAMAS sensors, can guarantee that all particles passing through the sensor are counted.

This results in better statistical analysis and prevents the loss of information compared to in-situ cells that detect only a small portion of the whole sample flow.

### Calibration

The Automatic Particle Counter is calibrated according to International Calibration Standards. The calibration is traceable to Standard Reference Material® of the NIST (National Institute of Standards and Technology). More than one calibration can be preconfigured in a single system.

### Standards

Display shows particle numbers, cleanliness classes and size. Printout according to many international standards (e.g. IP 577, DEF STAN 91-91, ISO 4406, NAS 1638, SAE AS 4059, GJB 420, GOST 17216 and NAVAIR 01-1A-17).

### Carrying bag:

The optional carrying bag for the rugged case PAMAS GO is equipped with a shoulder strap and with three handy side pockets.

### Technical data

#### Sampling system:

- Wear resistant ceramic piston pump with controlled constant flow.

#### Pressure range:

- From pressureless up to 6 bar (85 psi)

#### PAMAS Volumetric Sensor: PAMAS HCB-LD-50/50

Calibration ranges:

- 4 - 70 µm(c) according to ISO 11171 (standard calibration)
- 2 - 100 µm according to ISO 4402 (optional calibration)

Max. particle concentration: 24,000 p/ml at a nominal flow rate of 25 ml/min and a coincidence rate of 7.8%.

#### Counter:

- 8-channel particle counter
- 32-bit high performance CPU with sophisticated programmable digital domain signal conditioning and 4096 internal channels
- Data printout: 32 column thermo printer
- Data transfer: 8 bit ASCII code through USB port (57600 baud)
- Power supply: 90-240 V AC / 50-60 Hz or 12-30 V DC or via integrated battery for up to 3 hours operation
- Weight: approximately 8 kg
- Size: 340 mm x 220 mm x 420 mm

#### Options:

- Carrying bag



*Carrying bag for PAMAS GO case*



Management System  
ISO 9001:2015

www.tuv.com  
ID 9105038017

**PAMAS HEAD OFFICE** Dieselstraße 10, D-71277 Rutesheim, Phone: +49 7152 99 63 0, Fax: +49 7152 99 63-32, Email: info@pamas.de  
**PAMAS USA** 1408 South Denver Avenue, Tulsa, OK 74119 USA, Phone: +1 918 743 6762, Fax: +1 918 743 6917, Email: clay.biolo@pamas.de  
**PAMAS BENELUX** Mechelen Campus, Schaliënhoevedreef 20T, B-2800 Mechelen, Phone: +32 15 28 20 10, Mobile: +32 477 42 48 62, Email: paul.pollmann@pamas.de  
**PAMAS FRANCE** Route du Tailleur 210/136, F-40170 Saint-Julien-en-Born, Mobile +33 6 25 33 20 41, Email: eric.colon@pamas.fr  
**PAMAS LATIN AMERICA** Curitiba-Paraná, Brazil, Phone/Fax: +55 41 3022 5445, Mobile: +55 41 999 72 21 73, Email: marcelo.aiub@pamas.de  
**PAMAS INDIA** No. 203, I floor, Oxford House, #15 Rustam Bagh Main Road, Bangalore 560017, India, Phone: +91 80 41 15 00 39, Email: info@pamas.in  
**PAMAS HISPANIA** Calle Zubilleta No. 13 1ºB, ES-48991 Algorta, Mobile: +34 67 75 39 699, Email: julian.malaina@pamas.de  
**PAMAS UK** Sci-Tech Daresbury, Keckwick Lane, Daresbury, Cheshire WA4 4FS, Mobile: +44 79 17 71 33 66, Email: graeme.oakes@pamas.de

**Besuchen Sie uns im Internet: [www.pamas.de](http://www.pamas.de)**